








| 版本/Rev. | 日期/DATE   | 说明/DESCRIPTION       | 备注/REMARK | 批准/APPROVER |
|---------|-----------|----------------------|-----------|-------------|
| 00      | 2024/9/27 | 首次发布/Original vesion |           |             |




Power input: DC5521, 12V-2A

Optical window area, blocked is forbidden



Ethernet

LED indicator



- Notes:
1. Unit: mm
  2. Tolerance:  $\pm 0.2$
  3. Dimension: L108\*W97\*H88
  4. Weight:  $505 \pm 5g$
  5. 4x "M2.5\*P0.45" screw hole are designed on bottom sides
  6. 1x "1/4 UNCT" screw hole is designed on bottom center
  - 7 Interface: 1x Power input (DC5521, 12V-2A);  
1x Ethernet (RJ45); 1x USB-C; 1x LED indicator
  8. Optical window of lidar or two cameras  
are blocked is forbidden during operation

|                 |                                                                                     |
|-----------------|-------------------------------------------------------------------------------------|
| 比例/SCALE<br>1:1 | SLAMTEC 上海思岚科技有限公司<br>Shanghai Slamtec Co., Ltd                                     |
| 单位/UNIT<br>MM   |                                                                                     |
| 名称/PART NAME:   | Aurora-机械尺寸                                                                         |
| 图号/DRAWING NO.: | ARRC-A000-00                                                                        |
| 图例              | See more products please visit <a href="http://WWW.SLAMTEC.COM">WWW.SLAMTEC.COM</a> |